



## **DEPOLOX® 400 M ANALYZER FOR POTABLE WATER**

### **WALLACE & TIERNAN® ANALYZERS/CONTROLLERS**

The DEPOLOX® 400 M system is an on-line analyzer designed to measure the disinfectant concentration in drinking and other clean water applications.

The state of the art electronics incorporates a color touch screen the size of today's popular smart phones making the user interface truly intuitive. Communication with the instrument includes a standard Ethernet port which allows access to built-in web visualization of all pertinent information when connected to a local area network. An RS 485 port and four mA outputs are also standard for communication to other plant monitoring and control systems.

All popular disinfectants utilized today can be measured including: free chlorine, total chlorine, chlorine dioxide, ozone and potassium permanganate. Choose from two types of amperometric disinfectant measurements for use with the new electronics: unless water quality dictates otherwise, the well proven, lowest life cycle cost and extremely fast reacting DEPOLOX 5 C bare electrode measurement is the obvious choice; otherwise choose from a number of membrane based amperometric sensors fitted into our precisely flow controlled VariaSens™ C flow cell. A temperature measurement is standard and there is a choice of adding either an additional pH measurement, an ORP or a fluoride measurement.

The electronics includes smart operation features such as user configured calibration and service reminders. Instructions are provided on how to set up the analyzer to be compliant with calibration check intervals required by regulatory agencies. The new flow cell LED light indication changing color along with user defined alarm text can easily alert personnel to perform a required calibration check.

### **Benefits**

- Intuitive operation as well as easy visualization of all measured parameters via a 4" color touch panel
- LED lit flow cell that can be programmed to change color in case of an alarm or fault condition
- Data logging of measurement values with easy transfer to remote devices
- Smart operation features: user configured intervals for calibration checks and also for the instrument's service intervals
- State of the art communication possibilities via an Ethernet interface (Modbus® TCP) as well as a RS 485 port
- Very fast reaction to a change in disinfectant concentration with the popular DEPOLOX bare electrode measurement

## ELECTRONIC MODULE

### Touch panel:

4 inch capacitive color touchscreen with backlight

### Measurement inputs:

Rugged 3-electrode sensor DEPOLOX® 5 C for free chlorine,  $\text{ClO}_2$ ,  $\text{O}_3$ ,  $\text{KMnO}_4$  or 1 x VariaSens™ flow cell with a choice of membrane sensors: FC2 - free chlorine, TC3 - total chlorine, OZ7 - ozone, CD7 - chlorine dioxide and sensors 1 x pH or 1 x ORP or 1 x fluoride & 1 x temperature

### Digital inputs:

5 x freely definable

### Output contacts:

Max. six freely definable fused alarm contacts/general fault messages

Relay status is depicted on the display;  
max. 3.15 A /250 V AC; 0.2 A/220 V DC

### Analog outputs:

4 x 0/4 - 20 mA, freely configurable  
Load  $\leq$  500 Ohm, accuracy  $<$  0.5 % FS  
Galv. isolated up to 50 V relative to earth

### Interfaces:

Ethernet interface (HTTP protocol/Modbus® TCP protocol); RS 485 to connect to the Wallace & Tiernan® Process Monitoring System (option)

### Power supply:

100 - 240 V AC  $\pm$  10 %, 50/60 Hz, 48 VA  
24 V DC  $\pm$  20 % 30 W

**Ambient temperature:** 0 - 50 °C (32 - 122 °F)

**Protection:** IP 66

**Tests and marks:** Conform to CE, CSA

**Weight (incl. packaging):** 4.5 kg (9.9 lbs)

**Dimensions (W x H x D):**

320 x 311 x 153 mm (12.6 x 12.2 x 6.0 ")

## DEPOLOX 5 C FLOW CELL MODULE

The DEPOLOX 5 C flow cell houses the amperometric bare electrode. Stable measuring signals are achieved with hydrodynamic grit cleaning together with optimized flow around all sensors.

## VARIASENS C FLOW CELL MODULE

The VariaSens™ C flow cell houses one disinfectant based amperometric membrane sensor.

Both flow cells include a temperature measurement and can include either an optional pH or a fluoride measurement. The flow cells are available as discharge to a gravity drain or to a pressurized line. The following components are integral to both of the above mentioned flow cells.

### Flow control valve:

- Controlled sample water flow: 33 l/h (0.15 US gpm)
- Control range: 0.25 - 3.0 bar (3 - 60 psi at valve inlet)
- Back-pressure: max. 1.5 bar (21.7 psi) for press. model
- Sample water temperature: max. 50 °C (122 °F)

### Multi-sensor:

- Monitoring of correct sample water flow  
Switching point: 21 l/h +/- 3; Switching hysteresis: 2 l/h
- Measurement of sample water temperature with sensor Pt 1000 for the temperature compensation of the chlorine and possibly the pH measurement
- Sample water earthing with stainless steel sleeve

### Sample water connections:

PVC hose 6 x 3 mm or PE hose 6 x 1 mm hose connector adaptors to 1/2 " threaded hose connection

**Weight (incl. packaging):** approx. 2.5 kg (5.5 lbs)

### Dimensions (W x H x D):

253 x 375 x 163 mm (9.9 x 14.7 x 6.4 ")

## MEASURING RANGES

**DEPOLOX 5 sensor: free chlorine,  $\text{ClO}_2$ ,  $\text{O}_3$ ,  $\text{KMnO}_4$ :**  
0 to 20 mg/l ; min 200  $\mu\text{S/cm}$

**pH:** pH 0 to 12 (short time to 14)

**ORP:** 0 to 1000 mV, scale freely selectable in 100 mV steps

**pH compensation (free chlorine measurement with DEPOLOX 5 sensor):** within the pH range of 5.0 - to 8.0

**Fluoride:** 0 to 20 mg/l

**FC2 membrane sensor; Free chlorine:** 0 to 10 mg/l

**TC3 membrane sensor; total chlorine:** 0.05 to 10 mg/l

**CD7 membrane sensor; chlorine dioxide:** 0 to 10 mg/l

**OZ7 membrane sensor; ozone:** 0 to 10 mg/l



Auf der Weide 10, 89312 Günzburg, Germany

+49 (8221) 904-0 [www.evoqua.com](http://www.evoqua.com)

DEPOLOX, VariaSens and Wallace & Tiernan are trademarks of Evoqua Water Technologies LLC, its subsidiaries or affiliates, in some countries. MODBUS is a trademark of Schneider Electric USA, Inc. All information presented herein is believed reliable and in accordance with accepted engineering practices. Evoqua makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Evoqua assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.

© 2019 Evoqua Water Technologies GmbH Subject to change without notice WT.050.700.000.IE.PS.1219

Wallace & Tiernan® Products worldwide

**Australia**  
+61 1300 661 809  
info.au@evoqua.com

**Canada**  
+1 905 944 2800  
wtoc.can@evoqua.com

**China**  
+86 21 5118 3777  
sales.cn@evoqua.com

**France**  
+33 1 41 15 92 20  
wtfra@evoqua.com

**Germany**  
+49 8221 9040  
wtger@evoqua.com

**Singapore**  
+65 6559 2600  
sales.sg@evoqua.com

**UK**  
+44 300 124 0500  
info.uk@evoqua.com

**USA**  
+1 800 524 6324  
wt.us@evoqua.com